

DMS7-550M/DHP7-550/DMS7

**LCD Digital 7-Inch Timed Heating Magnetic Stirrer
(Strong Magnetic)、 Hotplate、 Magnetic Stirrer**

DMS4-550/DHP4-550/DMS4

**LCD Digital 4-Inch Timed Heating Magnetic Stirrer、
Hotplate、 Magnetic Stirrer**

Features

- Ceramic discs are extremely corrosion-resistant, resistant to strong acids and alkalis, and high temperatures, making it easy to clean accidental drips of solvents, oils, or other contaminants.
- The corrosion-resistant all-metal housing provides good heat dissipation and reliable fire protection.
- High-efficiency infusion platform and waterproof edge design prevents liquid from entering the interior of the machine and corroding electronic components.
- Selected high-temperature resistant strong magnetic magnet, strong stirring, suitable for viscous liquid stirring.
- Heating modes are divided into: A rapid heating mode, B standard heating mode, C stable heating mode, to meet different customer needs.
- Safety locks to prevent accidental changes in operating conditions.
- Buzzer: When the machine malfunctions, or the timer function counts down to the end of the buzzer will emit a "drip drip drip" sound.
- Residual heat warning function, when the disc temperature is higher than 50 °C, turn off the heating, the screen will have a "HOT" flashing prompt, even if the power off, the display is still "HOT" flashing to remind the high temperature.
- Two independent safety circuits are designed to continuously monitor the equipment. When overheating occurs, the sensor fails, the machine reports an error and stops heating, and when the line is short-circuited, the machine automatically cuts off the power supply to protect the operator's safety.
- DC brushless motor, no spark, long life; low noise, maintenance-free, smooth running.
- The LCD displays the set and real-time values of speed, time and temperature in an intuitive and clear manner.
- Timing function, timing range 1min-99h59min, countdown to the end of the stop heating, will not stop stirring, so as not to heat damage to the sample.
- Remote control function with PC connection.
- Safety temperature can be set.



Specifications	DMS4-550	DHP4-550	DMS4
Working plate size	100x100mm (4 inch)	100x100mm (4 inch)	100x100mm (4 inch)
Plate Material	Glass Ceramic	Glass Ceramic	Glass Ceramic
Motor type	Brushless DC motor	-	Brushless DC motor
Stirring positions	1	-	1
Maximum stirring volume [H ₂ O]	10L	-	10L
Maximum stirrer size [length]	40mm	-	40mm
Speed range and step	50~1500rpm, step 1rpm	-	50~1500rpm, step 1rpm
Speed Display	LCD	-	LCD
Temperature display	LCD	LCD	
Heating temperature range	Room temp-550°C, increment 1°C	Room temp-550°C, increment 1°C	-
Temperature control accuracy of heating liquid	±1°C(<100°C)±1%(>100°C)	±1°C(<100°C)±1%(>100°C)	-
overheating protection	580°C	580°C	-
Temperature display accuracy	0.1°C	0.1°C	-
External temperature sensor	PT1000 (accuracy±0.2°C)	PT1000 (accuracy ±0.2°C)	-
Waste heat warning function	50°C	50°C	-
Data connection	RS232	RS232	RS232
Protection class	IP21	IP21	IP21
Timer function	1min-99h59min	1min-99h59min	1min-99h59min
Motor output power	10W	-	10W
Power	460W	430W	30W
Heating output power	410W	410W	-
Voltage,Frequency	100-120/200-240V, 50/60Hz	100-120/200-240V, 50/60Hz	100-240V, 50/60Hz
Dimensions [L x W x H]	270x175x108mm	270x175x108mm	270x175x108mm
Weight	2.2kg	1.8kg	1.8kg
Permissible ambient temperature and humidity	5-40°C, 80%RH	5-40°C, 80%RH	5-40°C, 80%RH